




ITEM #	PART #	QTY	DESCRIPTION	MATERIAL
1	AJ-156-11	1	HOUSING, JACK CABLE	#303 STAINLESS STEEL
2	AJ-165-30	1	INSERT 5-COND, CRIMP SLEEVE	DIALLYPHTHALATE, TYPE SDGF & GOLD PLATED BRASS
3	AP-105-5	1	STRAIN RELIEF	NYLON
4	AP-116-3	1	WASHER	RUBBER
5	AP-136-8	1	NUT ADAPTER	BRASS, BLACK CHROME
6	AP-136-6	1	CLAMP SHIELD, OUTER	NICKEL PLATED BRASS
7	AP-136-5	1	CLAMP SHIELD, INNER	NICKEL PLATED BRASS
8	SEE TABLE #1	1	BUSHING	RUBBER
9	SEE TABLE #1	1	WASHER	STAINLESS STEEL
10	SEE TABLE #1	1	SPRING	#302 STAINLESS STEEL
11	AP-116-6	1	STUD	ANODIZED ALUMINUM ALLOY

NOTES:
1) MARK PART NUMBER & MANUFACTURERS NAME, LOCATED APPROXIMATELY AS SHOWN.



SECTION Z-Z

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

						DWN.BY	HR	DATE	6/10/14	MATERIAL					
						CHECKED BY		DATE		FINISH					
						APPR.BY		DATE		WEIGHT		SCALE = 2.00 :1		NEXUS STAMFORD,CONN	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES & OR [mm]			TITLE						
						TOLERANCES: DECIMAL:									
						±.XX(X.X) ±.XXX(X.XX) ±.XXXX(X.XXX)			JACK 5-PIN AUDIO, CRIMP SLEEVE			SIZE		DWG. NO.	
						±.0X(0.X) ±.00X(0.0X) ±.000X(0.0XX)									
A	NEW RELEASE		202	6/10 2014	HR	FRACTION: ±X/XX ± X/XX			ANGLES: ± X ° ± X °			DO NOT SCALE DWG.		SHEET 1 OF 1	
LET.	REVISION			CN #	DATE	CHK								AJ-165S	