





DESCRIPTION: M12 FEMALE - PANEL MOUNT (REAR) - 4 POS.



PANEL CUTOUT



NUT



NOTE:

MATERIAL

HOUSING:

CONTACT:

NUT:

SHELL:

O-RING:

FINISH:

CONTACT:

PBT UL94V-0, BLACK  
BRASS  
BRASS  
BRASS  
EPDM, BLACK

GOLD PLATED  
OVER 50 $\mu$  NICKEL  
NICKEL PLATED  
NICKEL PLATED

ELECTRICAL

RATED CURRENT:

4A  
250V

INSULATION RESISTANCE:

100 M $\Omega$ ms MIN.

CONTACT RESISTANCE:

10 m $\Omega$ ms MAX.

WATER PROOF:

IP67

ENVIRONMENT


OPERATION TEMPERATURE:

-40°C TO +85°C

860-004-213R00Y

3 = BRASS/NICKEL SHELL & NUT  
S = STAINLESS STEEL SHELL & NUT

1 = GOLD FLASH  
4 = 10 $\mu$  GOLD



PCB LAYOUT

RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON DATE: 03-07-16

NorComp

SCALE: NTS SHEET 1 OF 1 REV 4

DWG NO. 860-004-213R00Y