







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190346	2019/03/05	Vicky	Change Note



Recommended Panel
Cut-Out




With Liquid Glue



Note:


- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP67, Unmated.
- * Housing: Thermoplastic, Black
- * Pin: Copper Alloy, Gold Plated.
- * Nut: Thermoplastic, Black.
- * Gasket: Rubber, Gray.
- * Use with waterproof cap or dust cap
Maximum Panel Thickness: 2.8mm
- * Use without waterproof cap or dust cap
Maximum Panel Thickness: 4.0mm
- * Gasket and Nut are packed separately
in PE bags. (Gasket/Nut不組裝, 散裝出貨)

ABD-XXPMFS-LC7001
02: 2Pin
06: 6Pin




6 Pin


Pin Assignments
Front View




5 Pin



4 Pin




3 Pin



2 Pin

Pin Assignments Front View

UNIT: mm



TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE
STANDARD
PANEL LOCK M CONN F PIN

SCALE 3:2 SIZE A4 SHEET 1 OF 1

REV. B WC-REV. A.1 QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO.	DRAWN BY	DATE
DWG. NO.	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
ALTW	Max	2019-03-05