








- NOTES:
- 1. ALL PARTS TO BE BULK PACKED
 - 2. CONTACTS SHIPPED UNASSEMBLED
 - 3. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE

ASS'Y P/N	FOR CABLE O.D.
W18980-XSG-P-518	.175-.185 [4.4-4.7]
W18980-XSG-P-521	.205-.215 [5.2-5.5]
W18980-XSG-P-522	.215-.225 [5.5-5.7]

ASS'Y P/N	CONTACT QTY	KEY STYLE
W18980-5SG-P-5XX	5	A-KEY
W18980-6SG-P-5XX	6	B-KEY
W18980-7SG-P-5XX	7	A-KEY
W18980-XSG-P-5XX		



DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS

SHOWN ASSEMBLED
FOR CUSTOMER REFERENCE ONLY

GROMMET SIZE
NUMBER OF CONTACTS

CUSTOMER APPROVAL			
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.			
APPROVED BY: _____		DATE: _____	

RoHS COMPLIANT

A	MA	08-24-20	RELEASED PER PDR 18004						
	JGK	8/29/19	DRAWING CREATED FOR PDR #18004.						
REV.	INIT.	DATE	DESCRIPTION						
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: JGK		DATE: 8/29/19		 601 E. WILDWOOD VILLA PARK, IL 60181		
			CHECKED BY:						
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			APPROVED BY:		TITLE: CABLE TO CABLE CONN. ASS'Y (5-7) #26 SOCKET CONTACTS, CRIMP INSTA-CLICK™ MICRO-CON-X STANDARD PRODUCT				
			SCALE NTS		SIZE B	SHEET 1 OF 1		CUSTOMER:	
▷	= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX		FILE: W18980-XSG-P-5XX		DIRECTORY: SLW		PART NUMBER: W18980-XSG-P-5XX		REV A