









Mating Cycles	500
Filter type	C
Capacitance	1000pf±20%
Working Voltage	100V
Current Rating	7,5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	1 dB
10	3 dB
50	12 dB
100	20 dB
500	34 dB
1000	30 dB

PCB layout, component side
thickness 1,6



0964 314 7234	4-40 UNC
0964 314 7235	M3
Part number	Screw-lock thread

All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.		Ref.	
All rights reserved Department EL PD		Created by ZHUANGJ	Inspected by LUOK	Standardisation HOFFMANN	Date 2018-08-28	State Final Release
HARTING Electronics GmbH D-32339 Espelkamp		Title D-Sub female angled 25-pole turned solder pins				Doc-Key / ECM-Nr. 100801512/UGD/000/A 500000139092
Type TB		Number 0964314723X				Rev. A
						Page 1/1