

F

E

D

C

B

A

F

E



D

C




B

A

10 9 8 7 6 5 4 3 2 1



CIRCUITS	ORDER NO.	DIM. C	DIM. D	DIM. A
2	89400-02I*	2.00	0.75	6.00
3	89400-03I*	4.00	2.00	8.00
4	89400-04I*	6.00	4.00	10.00
5	89400-05I*	8.00	6.00	12.00
6	89400-06I*	10.00	8.00	14.00
7	89400-07I*	12.00	10.00	16.00
8	89400-08I*	14.00	12.00	18.00
9	89400-09I*	16.00	14.00	20.00
10	89400-10I*	18.00	16.00	22.00
11	89400-11I*	20.00	18.00	24.00
12	89400-12I*	22.00	20.00	26.00
13	89400-13I*	24.00	22.00	28.00
14	89400-14I*	26.00	24.00	30.00
15	89400-15I*	28.00	26.00	32.00
16	89400-16I*	30.00	28.00	34.00




PART NO. LEGEND
89400 - ** I *

CT SIZE

COLOR OPTION
0 - NATURAL (WHITE)
1 - BLACK
2 - RED
3 - YELLOW
4 - BLUE
6 - GREEN

NOTE:

- MATERIALS : HOUSING - NYLON (PA66), UL94 V-0
COLOR : SEE OPTION
TERMINAL - BRASS
- FINISHES : TERMINAL - TIN THICKNESS 1.27-2.54 MICROMETER OVER
NICKEL THICKNESS 2.54 MICROMETER MIN OVERALL
COPPER THICKNESS 1.07 MICROMETER MIN OVERALL
- PRODUCT SPECIFICATION : PS-87369-0001
- BULK PACK IN PVC BAG WITH 1000 PCS PER BAG.



NEW RELEASE EC NO: SH2006-0288 DRW:DHU CHKD:HARVEY APPR:GCHEN	QUALITY SYMBOLS =0 =0	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 					
				mm	INCH	DRAWN BY GOH	DATE 1995/02/04	TITLE 2.00MM WIRE-BOARD STRAIGHT HEADER						
			4 PLACES	± ---	± ---	CHECKED BY	DATE							
			3 PLACES	± ---	± ---	APPROVED BY		DATE	MOLEX INCORPORATED					
			2 PLACES	± 0.2	± ---									
			1 PLACE	± ---	± ---	MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-89400-***1*	SHEET NO. 1 OF 1					
			ANGULAR ± ---°											
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						