


DRAWING MADE IN AMERICAN PROJECTION


REVISIONS

ZONE	LTR	DESCRIPTION	DATE	APPROVED
	F1	REVISED PER ECO-11-005030	24MAR11	HMR

.125 DIA.
MAX (TYP)





MFG'S NAME, BRAND OR LOGO
AND DATE CODE MARKED NEAR SIDE



MARKED ON FAR SIDE

- ① M24308/2-12F (-1, -2 & -3 ONLY)
- ② M24308/6-12F (-4, -5 & -6 ONLY)



-	X	-	-	-	-	MIL No.	M24308/6-12F	MARKED ON PACKAGE			
-	-	-	-	X	-	MIL No.	M24308/2-12F	MARKED ON PACKAGE			
X	-	-	-	-	-	MIL No.	M24308/6-18F	MARKED ON PACKAGE			
-	-	-	X	-	-	MIL No.	M24308/2-18F	MARKED ON PACKAGE			
1	1	1	-	-	-	C	204502-2	RECEPTACLE ASSY, SIZE 2 (BRASS SHELL)	4		
26	26	-	26	26	-	B	204351-1	CONTACT, SOCKET, SIZE 22D	3		
1	-	1	1	-	1	B	91067-1	INSERTION/EXTRACTION TOOL	2		
-	-	-	1	1	1	C	204502-1	RECEPTACLE ASSY, SIZE 2 (STEEL SHELL)	1		
6	5	4	3	2	1	DWG SIZE	NUMBER	NAME	ITEM No.		
204514	204514	204514	204514	204514	204514	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS ± .005 ANGLES ± .005				CONTRACT NO. DR. <i>11/30/70</i> CHK. <i>12-3-70</i> APPD. <i>12-9-70</i> REL. <i>12-9-70</i> DSGN APPD. OTHER APPD.	TE Connectivity STE NAME KIT, "HDD" SERIES, RECEPTACLE, SIZE #2 (26 POS.)
035	035	035	035	035	MATERIAL #						
						SCALE #				SHEET 1 OF 1	

△ SUPD BY 206501-44 (26) 206071-1

CUSTOMER DRAWING