





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	17DEC2019	AY	PS

- NOTES:
- MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0;COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE : MIN. 0.38 µm GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE : MIN. 2.0 µm BRIGHT TIN OVER NICKEL UNDER PLATING.
 - PACKAGING: TAPE AND REEL (WITH PICK AND PLACE CAP).
 - TOLERANCE NOT CUMULATIVE.
 - CUTTING BURR MAX. 0.25 mm




0.10	A	2*02-2*15 POS
0.15	A	2*16-2*25 POS

ALL CONTACTS



RECOMMENDED PCB PATTERN



1-2842143-0 AS SHOWN

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09AUG2019 SUBHASREE S	TE Connectivity		
		CHK 13AUG2019 KARTHIK JK			
		APVD 14AUG2019 PRASHANTH S			
		PRODUCT SPEC			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME AMPMODU 2mm BREAKAWAY HEADER, DUAL ROW, VERTICAL SMD, 0.38Au TR, WITH PICK AND PLACE CAP		
		0 PLC ±0.2	SIZE		
		1 PLC ±0.15	CAGE CODE		
		2 PLC ±0.15	DRAWING NO		
		3 PLC ±0.15	RESTRICTED TO		
		4 PLC ±0.15	A3 00779 ©=2842143		
		ANGLES ±2°	SCALE 5:1		
MATERIAL SEE NOTES		FINISH SEE NOTES	SHEET 1 OF 1		
			REV A1		
			CUSTOMER DRAWING		