

## Coaxial Panel Connector 22\_BNC-75-0-4/133\_N

### Description

Straight bulkhead receptacle jack

Interface standards

Interface compatible with IEC 61169-8



### Technical Data

#### Electrical Data

Impedance	75 Ω
Interface frequency max.	1 GHz

#### Mechanical Data

Number of matings	500
Weight	0.0072 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00071690
Catalogue drawing	DCA-00010480
Mounting hole	DOU-00008762

### Ordering Information

Single package	22_BNC-75-0-4/133_NE
----------------	----------------------