



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	13JUN2015	GY	CW
	A1	ECR-18-012802	18AUG2018	WQR	CW
	A2	ECR-18-009564	13SEP2018	CD	CW
	B	ECR-20-012892	19MAY2021	BS	CW

TYPE 1 / 类型 1




PG/M	THREAD
PG/M	螺紋
PG/M	螺紋

TYPE 2 / 类型 2



All dimension is same as TYPE 1, except those defined in this TYPE
除了已定义的尺寸外, 其余尺寸参考类型 I



T1912162125-001	POWDER COATED, DEEP GREY 表面喷涂, 深灰色	H16BPR-TSHC-M25	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,DEEP GREY,NO LOGO H16BPR上壳, 中部锁定, 侧出M25, 深灰色粉末喷涂, 无LOGO	M25	TYPE 2 类型2
T1912162132-001	POWDER COATED, DEEP GREY 表面喷涂, 深灰色	H16BPR-TSHC-M32	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY M32,POWDER COATED,DEEP GREY,NO LOGO H16BPR上壳, 中部锁定, 侧出M32, 深灰色粉末喷涂, 无LOGO	M32	
T1912162140-001	POWDER COATED, DEEP GREY 表面喷涂, 深灰色	H16BPR-TSHC-M40	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY M40,POWDER COATED,DEEP GREY,NO LOGO H16BPR上壳, 中部锁定, 侧出M40, 深灰色粉末喷涂, 无LOGO	M40	
T1912160140-100	POWDER COATED, BLACK 表面喷涂, 黑色	H16BPR-TSHC-M40	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY M40,POWDER COATED,BLACK,NO LOGO H16BPR上壳, 中部锁定, 侧出M40, 黑色粉末喷涂, 无LOGO	M40	
T1912161140-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H16BPR-TSHC-M40	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY M40,POWDER COATED,SILVER WHITE H16BPR上壳, 中部锁定, 侧出M40, 银白色粉末喷涂	M40	TYPE 1 类型1
T1912161132-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H16BPR-TSHC-M32	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY M32,POWDER COATED,SILVER WHITE H16BPR上壳, 中部锁定, 侧出M32, 银白色粉末喷涂	M32	
T1912161129-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H16BPR-TSHC-PG29	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY PG29,POWDER COATED,SILVER WHITE H16BPR上壳, 中部锁定, 侧出PG29, 银白色粉末喷涂	PG29	
T1912161125-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H16BPR-TSHC-M25	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,SILVER WHITE H16BPR上壳, 中部锁定, 侧出M25, 银白色粉末喷涂	M25	
T1912161121-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H16BPR-TSHC-PG21	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,SILVER WHITE H16BPR上壳, 中部锁定, 侧出PG21, 银白色粉末喷涂	PG21	
T1912160140-000	POWDER COATED, BLACK 表面喷涂, 黑色	H16BPR-TSHC-M40	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY M40,POWDER COATED,BLACK H16BPR上壳, 中部锁定, 侧出M40, 黑色粉末喷涂	M40	
T1912160132-000	POWDER COATED, BLACK 表面喷涂, 黑色	H16BPR-TSHC-M32	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY M32,POWDER COATED,BLACK H16BPR上壳, 中部锁定, 侧出M32, 黑色粉末喷涂	M32	
T1912160129-000	POWDER COATED, BLACK 表面喷涂, 黑色	H16BPR-TSHC-PG29	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY PG29,POWDER COATED,BLACK H16BPR上壳, 中部锁定, 侧出PG29, 黑色粉末喷涂	PG29	
T1912160125-000	POWDER COATED, BLACK 表面喷涂, 黑色	H16BPR-TSHC-M25	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,BLACK H16BPR上壳, 中部锁定, 侧出M25, 黑色粉末喷涂	M25	
T1912160121-000	POWDER COATED, BLACK 表面喷涂, 黑色	H16BPR-TSHC-PG21	H16BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,BLACK H16BPR上壳, 中部锁定, 侧出PG21, 黑色粉末喷涂	PG21	
PART NUMBER 料号	SURFACE TREATMEN 表面处理	DESCRIPTION 描述		PG/M THREAD PG/M 螺纹	TYPE 类型

NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY.
SURFACE TREATMENT: SEE TABLE.
DEGREE OF PROTECTION: IP68 (MATED).

1. 技术参数：
壳体材料： 铝合金。
表面处理： 见表格。
防护等级： IP68（配合）。

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 13JUN2015 Gino.Yao CHK 13JUN2015 Chris.Wang APVD 13JUN2015 Xiang.yu PRODUCT SPEC 108-137014 APPLICATION SPEC 114-137014		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		NAME H16BPR-TSHC-PG/M	
		WEIGHT -		SIZE A2	CAGE CODE -
MATERIAL - -		Customer Drawing		DRAWING NO C-T191216XXXXX00	RESTRICTED TO -
		SCALE 1:1		SHEET 1 OF 1	REV B