



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of product	Harmony 9001K
Product or component type	Security control station
Device short name	9001KY
Lock type	Complete with core, 6 tumbler pins

Complementary

Size	30 mm
Enclosure/cubicle description	Flush mounting
Enclosure material	Stainless steel
Type of installation	Indoor
Control station composition	1 key selector switch with spring return operator, OPEN-CLOSE marking 1 pushbutton, STOP marking
Type of keylock	Best
Key withdrawal position	Center
Connections - terminals	Screw clamp terminal
[Ue] rated operational voltage	300 V
[Ie] rated operational current AC	15 A
Product weight	4.98 lb(US) (2.26 kg)


Environment

NEMA degree of protection	NEMA 1
Environmental characteristic	Waterproof
Product certifications	CE CSA UL listed
Ambient air temperature for operation	-13...140 °F (-25...60 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901853275
Nbr. of units in pkg.	1
Package weight(Lbs)	5
Returnability	N
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
- - - - - Substance 2	Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------