

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2019-04-12	Allen Pan	03版轉A
B	CI90737	2019-05-13	Allen Pan	取消半成品階ZSE00108751,增加檢驗尺寸

F







E

D

C

B


A



Recommended PCB Layout
General tolerance: ± 0.05 mm

Notes:

- * Rated Voltage: 63V DC.
- * Rated Current: 16A.
- * Operating Temperature: $-25\sim 105^{\circ}\text{C}$.
- * Housing: Thermoplastic, Black.
- * Pin: Copper Alloy, Gold Plated.
- * Gasket: Rubber, Black.
- * Spring: Metal.
- * Packing: Tray.
- * Gasket is packed separately in PE bags.



UNIT:mm			TITLE MI2 L CODE, PANEL, THRU HOLE TYPE 5PIN, FEMALE CONN.		
TOLERANCE	.X ± 0.25	.XX ± 0.1	SCALE 2:1	SIZE A4	SHEET 1 OF 1
.XXX ± 0.05			REV. B	WC-REV. A.9	QC: Inspection item
ANGLES $\pm 2^{\circ}$					

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO MI2L-05PFFP-EE0001	DRAWN BY Allen Pan	DATE 2019-05-13
DWG NO MI2L-05PFFP-EE0001	CHECKED BY Fred Lee	DATE 2019-05-13
CUSTOMER ALTW	APPROVED BY Fred Lee	DATE 2019-05-13