



1	2	3	4
			



 Note:

- * RoHS Compliant
- *  Important Dimension
- * Waterproof rate: IPX7, mated
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - Extension Nut: Metal
 - Nut: Metal
 - O-Ring: Rubber, Gray
- * Clamp Ring: Metal
- * O-Ring: Rubber, Gray
- * Clamp Cage: Thermoplastic, Black
- * Sealing Nut: Metal
- * Seal: Rubber, Gray, OD: $\varnothing 4.0\text{mm} \sim \varnothing 7.0\text{mm}$
- * One set unassembled in one pe bag



UNIT: mm				TITLE		N SEN, M12 A -SHLD, SCREW CABLE W/O SR, F, F, FI SCREW IN	
TOLERANCE				SCALE	SIZE	SHEET	OF
.X	± 0.25			1:1	A4	1	1
.XX	± 0.1						
.XXX	± 0.05						
ANGLES	±			REV. B	WC-REV. A.3	QC: Inspection item	

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Mila	DATE 2015-09-29
DWG NO MSAS-XXBFFB-SR7001	CHECKED BY Cary	DATE 2015-09-29
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2015-09-29