

4		3		2		1																																																																																																													
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS																																																																																																											
© COPYRIGHT — By —		ALL RIGHTS RESERVED.		G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD																																																																																																						
									H1	REVISED PER ECO-11-005027	12MAR11	RK	HMR																																																																																																						
1 1.606 MAX AMP 16-14* INSULATION BODY AMP WIRE RANGE 16-14 AWG STRANDED 1 STAMP AMP 16-14* APPROX AS SHOWN 2 WIRE INSULATION .190 MAX DIA. <table><tr><td colspan="2">2500</td><td colspan="2">ON TAPE, REEL</td><td colspan="2">2-55825-1</td></tr><tr><td colspan="2">50</td><td colspan="2">LOOSE PIECE</td><td colspan="2">8-55825-2</td></tr><tr><td colspan="2">1000</td><td colspan="2">LOOSE PIECE</td><td colspan="2">55825-1</td></tr><tr><td colspan="2">QTY</td><td colspan="2">PACKAGE TYPE</td><td colspan="2">PART NO</td></tr></table> <table><tr><td colspan="2">AMP INCORPORATED CUSTOMER SERVICE SYSTEMS</td><td colspan="2">MAX RECOMMENDED OPERATING TEMPERATURE: 125° C MAX</td><td colspan="2">THIS DRAWING IS A CONTROLLED DOCUMENT.</td></tr><tr><td colspan="2">FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS</td><td colspan="2">PRODUCT INFORMATION CENTER 1-800-522-6752</td><td colspan="2">DIMENSIONS: INCHES</td></tr><tr><td colspan="2">FOR APPLICATION TOOLING INFORMATION</td><td colspan="2">TOOLING ASSISTANCE CENTER 1-800-722-1111</td><td colspan="2">TOLERANCES UNLESS OTHERWISE SPECIFIED:</td></tr><tr><td colspan="2">FOR ORDER ENTRY</td><td colspan="2">1-800-526-5142</td><td colspan="2">FINISH</td></tr><tr><td colspan="2"></td><td colspan="2">THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.</td><td colspan="2">EDP TIN PLATED</td></tr></table> <table><tr><td colspan="2">DWN S S GOULDEN 6/93</td><td colspan="2" rowspan="4"> STE TE Connectivity SPLICE, SEALABLE HEAT SHRINKABLE </td></tr><tr><td colspan="2">CHK R HERSEY 6/93</td></tr><tr><td colspan="2">APVD B BARE 6/93</td></tr><tr><td colspan="2">PRODUCT SPEC —</td></tr><tr><td colspan="2">APPLICATION SPEC 408-4022</td><td colspan="2">NAME</td><td colspan="2">SIZE</td><td colspan="2">CAGE CODE</td><td colspan="2">DRAWING NO</td><td colspan="2">RESTRICTED TO</td></tr><tr><td colspan="2">WEIGHT —</td><td colspan="2">A3</td><td colspan="2">00779</td><td colspan="2">C-55825</td><td colspan="2"></td><td colspan="2">—</td></tr><tr><td colspan="8">CUSTOMER DRAWING</td><td colspan="2">SCALE NTS</td><td colspan="2">SHEET 1 OF 1</td><td colspan="2">REV H1</td></tr></table>														2500		ON TAPE, REEL		2-55825-1		50		LOOSE PIECE		8-55825-2		1000		LOOSE PIECE		55825-1		QTY		PACKAGE TYPE		PART NO		AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 125° C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: INCHES		FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		TOLERANCES UNLESS OTHERWISE SPECIFIED:		FOR ORDER ENTRY		1-800-526-5142		FINISH				THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		EDP TIN PLATED		DWN S S GOULDEN 6/93		STE TE Connectivity SPLICE, SEALABLE HEAT SHRINKABLE		CHK R HERSEY 6/93		APVD B BARE 6/93		PRODUCT SPEC —		APPLICATION SPEC 408-4022		NAME		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO		WEIGHT —		A3		00779		C-55825				—		CUSTOMER DRAWING								SCALE NTS		SHEET 1 OF 1		REV H1	
2500		ON TAPE, REEL		2-55825-1																																																																																																															
50		LOOSE PIECE		8-55825-2																																																																																																															
1000		LOOSE PIECE		55825-1																																																																																																															
QTY		PACKAGE TYPE		PART NO																																																																																																															
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 125° C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.																																																																																																															
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: INCHES																																																																																																															
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		TOLERANCES UNLESS OTHERWISE SPECIFIED:																																																																																																															
FOR ORDER ENTRY		1-800-526-5142		FINISH																																																																																																															
		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		EDP TIN PLATED																																																																																																															
DWN S S GOULDEN 6/93		STE TE Connectivity SPLICE, SEALABLE HEAT SHRINKABLE																																																																																																																	
CHK R HERSEY 6/93																																																																																																																			
APVD B BARE 6/93																																																																																																																			
PRODUCT SPEC —																																																																																																																			
APPLICATION SPEC 408-4022		NAME		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO																																																																																																									
WEIGHT —		A3		00779		C-55825				—																																																																																																									
CUSTOMER DRAWING								SCALE NTS		SHEET 1 OF 1		REV H1																																																																																																							