

6

5

4

3


2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/4/20	

**SPECIFICATIONS:**

Material:

Housing: PBT, rated UL 94V-0, Color: Blue

Cap: PBT, rated UL 94V-0, Color: Black

Electrical:

Standards of IEC, EIA/TIA, Telcordia

Insertion loss: 0.2dB max

Mechanism durability (500 cycles min): 0.2dB max

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS

TOLERANCES: EXCEPT AS NOTED

MM ANGLE

X. ± 0.35 X.* ± 2°

.X ± 0.30 .X* ± 1°

.XX ± 0.25 .XX* ± 0.5°

.XXX ± 0.15 .XXX* ± 0.5°

APPROVALS		DATE
DRAWN	OW	9/4/20
CHECKED	JL	9/4/20
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,

Union, NJ 07083

Phone: 908-687-5000

Fax: 908-687-5710

TITLE

SC TYPE ADAPTER, PC, 1 PORTS, LONG-EARED, WITH SC TWO
TYPE DUST CAP, TRANSPARENT FLAT BOTTOM BRACKET

SIZE

X

PART NO.

OPSB1ANNC1N1T3

REV.

-

REF:

S00005C

SCALE: NTS

SHEET 1 OF 1