






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/28/21	



SPECIFICATIONS:

Material:

Cage: Copper Alloy

Electrometric Gasket: Conductive Rubber

Cage Rear EMI Gasket: Conductive Foam

Front Flange: Zinc Alloy, Nickel plated

Front EMI Gasket: Copper Alloy, Matte Tin over Nickel underplate overall

Heat Sink Clip: Copper Alloy

Heat Sink: Aluminum, Nickel plated

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
 ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

mm	Angles
.X ± .25	±2°
.XX ± .13	
.XXX ± .10	

DRAWN	WX	5/28/21
CHECKED	RC	5/28/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
 AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
 PERMISSION FROM ADAM TECH





**ADAM
 TECH**

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE		REV.	
10 GIGABIT SMALL FORM FACTOR CAGE, 1PORT DIP TYPE, PRESS FIT, EMI CLIP W/ GASKET, W/ HEAT SINK		-	
SIZE	PART NO.		
X	XFC-1-CS2-EMI-PF-HSK		
REF:	S00005C	SCALE:	NTS
SHEET		1 OF 3	

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 3 FOR REVISION				



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

	mm	Angles
.X	$\pm .25$	$\pm 2^\circ$
.XX	$\pm .13$	
.XXX	$\pm .10$	

DRAWN	WX	5/28/21
CHECKED	RC	5/28/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		PART NO.		REV.
10 GIGABIT SMALL FORM FACTOR CAGE, 1PORT DIP TYPE, PRESS FIT, EMI CLIP W/ GASKET, W/ HEAT SINK		XFC-1-CS2-EMI-PF-HSK		-
SIZE	X	REF:	S00005C	SCALE: NTS
SHEET 3 OF 3				