




- 1 TIN PL .000150 MIN THK MIL-T-10727
- 2 .045 MAX BURR ALLOWED INSIDE THE WIRE BARREL ID IN AREA OF SIGHT HOLE.

CLEANED	650-750 MCM	COPPER	1-324468-0
1		ASTM-B-75 ANNEALED	324468
FINISH	WIRE RANGE	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
INCHES	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -

MATERIAL	FINISH
SEE TABLE	SEE TABLE

DWN	DK SCHRUM	4/24/89
CHK	MS FEHER	4/24/89
APVD	TL SHUTTER	4/24/89
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT	.395 LB.	
CUSTOMER DRAWING		

TE Connectivity

NAME	SPLICE, BUTT, AMPPOWER		
	WIRE SIZE: 700 MCM		
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=324468	-

SCALE	2:1	SHEET	1 OF 1	REV	N
-------	-----	-------	--------	-----	---