



Main

Range	Square D X Series
Product or Component Type	Cover frame
Accessory / separate part category	Installation accessory
Aesthetic name	X Series
Number of gangs	1 gang
Product destination	Socket-outlet
Color	Light almond

Complementary

Suitable for body type	Standard
Suitable for integrated connection type	1 socket-outlet
Size	M
Fixing Mode	Screw-fixed
Material	Plastic
Surface Finish	Matte
Height	5.20 in (132 mm)
Width	3.31 in (84 mm)
Depth	0.28 in (7 mm)
Quantity per Set	1 piece

Environment

Product Certifications	cULus
Standards	UL 514D

Ordering and shipping details

Category	09935-WD BASIC WALL PLATES
Discount Schedule	DE9
GTIN	785901566809
Nbr. of units in pkg.	1
Package weight(Lbs)	0.95 oz (27.0 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.28 in (0.7 cm)
Package 1 width	3.31 in (8.4 cm)
Package 1 Length	5.20 in (13.2 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	12.13 oz (344.0 g)

Package 2 Height	4.33 in (11 cm)
Package 2 width	3.54 in (9 cm)
Package 2 Length	5.71 in (14.5 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Weight	17.37 lb(US) (7.88 kg)
Package 3 Height	12.20 in (31 cm)
Package 3 width	9.25 in (23.5 cm)
Package 3 Length	18.70 in (47.5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	2 years
----------	---------