

# Han 24M-gs-M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 37 024 0523
Specification	Han 24M-gs-M40
HARTING eCatalogue	<a href="https://b2b.harting.com/19370240523">https://b2b.harting.com/19370240523</a>

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> M
Type of hood/housing	Hood
Description of hood/housing	Special type
Type	High construction

## Version

Size	24 B
Version	Side entry
Cable entry	1x M40
Locking type	Double locking lever
Field of application	Hoods/housings for rough environments

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
	IP66
	IP67
Type rating acc. to UL 50 / UL 50E	4
	4X
	12



**Pushing Performance**  
Since 1945

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

## Commercial data

Packaging size	1
Net weight	350 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140171305
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors