


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A5	ECR-09-023155	22OCT2009	VG	AR
	A6	ECR-10-009777	17MAY2010	SR	AR
	B	ECR-16-001983	20MAY2016	GCM	JB
	C	ECR-16-014579	10MAY2017	GCM	JB

Notes

- 1
- SUITABLE HOUSINGS: SERIES EMV, SIZE 1
CUSTOMER DRAWING 1102700, 1106402, 1106200
- 2
- STANDARDS:
DIN EN 61984, DIN EN 60664-1
- 3
- SUR TEC 650 CHROMIT AL TCP PASSIVATION
- 4
- TOOL:
PHILLIPS SCREWDRIVER PH1.
- 5
- VARNISH ON INSIDE AREA NOT NECESSARY
- 6
- PACKAGING:
10 SETS IN A CARTON.



PN 0-1 AS SHOWN

1					ANGLED BULKHEAD HOUSING		ALU	BLACK	SERIES EMV-K WITHOUT LOGO	8
1	1	1	1	1	SCREW COUNTERSUNK RAISED HEAD	-	STAINL. STEEL V2A	-	M3x8 PH1 DIN EN ISO 7047	7
1	1	1	1	1	O - RING	-	NBR	BLACK	3.0x1.0	6
1	1	1	1	1	PROGFILE SEAL	-	FKM	BLACK	SERIES EMV / HIP	5
	-	1	-	-	ANGLED BULKHEAD HOUSING	M20	ALU	BLACK SEE NOTE 3	SERIES EMV-K	4
	1	-	-	-	ANGLED BULKHEAD HOUSING	M20	ALU	GREY	SERIES EMV-K	3
	-	-	1	-	ANGLED BULKHEAD HOUSING	M16	ALU	BLACK SEE NOTE 3	SERIES EMV-K	2
	-	-	-	1	ANGLED BULKHEAD HOUSING	M16	ALU	GREY	SERIES EMV	1
0-5	0-4	0-3	0-2	0-1		"A"	MATERIAL	COLOR/SURFACE	NOTE	ITEM
PN/QTY					DESCRIPTION					

PARTS LIST (PER ONE UNIT)

0-5	EMV-K.3/4.SG-N
0-4	EMV.3/4.SG.1.M20.G
0-3	EMV-K.3/4.SG.1.M20.G
0-2	EMV-K.3/4.SG.1.M16.G
0-1	EMV.3/4.SG.1.M16.G
PART NO.	ORDERING TEXT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

±.1
±.1
±.1
±.1
±.1
±1°

FINISH
-

DWN
V.GLUMM
CHK
H.Braun
APVD
T.Schnurpfel

26AUG2009
26AUG2009
26AUG2009

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
ANGLED BULKHEAD HOUSING ASS'Y
SIDE ENTRY, SERIES EMV, SIZE 1
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1106401

RESTRICTED TO
-

SCALE
1:1

SHEET
1 OF 1

REV
C

1470-19 (3/13)