

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/8/20	

D

D

C


C

B







B

A

A



RECOMMENDED PCB LAYOUT

**SPECIFICATIONS:**

Material:

Housing: PBT, rated UL 94V-0, Color: See Chart

Cap: PBT, rated UL 94V-0, Color: Black

Sleeve: Zirconia Ceramic

Solder Foot: Copper Alloy, Nickel Plated

Electrical:

Standards of IEC, EIA/TIA, Telcordia

Low Insertion loss: 0.2dB max

Environmental:

Lead free, RoHS compliant.



OPSB1BNSC1N2	SC/PC, CUCURBIT TYPE DUST CAP	2184C Blue	PBT Black
OPSA1BNSC1N1	SC/APC, TWO TYPE DUST CAP	7737C Green	PBT Black
PART NUMBER	DESCRIPTION	Housing&Insert color	Cap Color

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED
MM ANGLE
X. ± 0.35 X* ± 2°
.X ± 0.30 .X* ± 1°
.XX ± 0.25 .XX* ± 0.5°
.XXX ± 0.15 .XXX* ± 0.5°

APPROVALS		DATE	
DRAWN	LH	9/8/20	
CHECKED	JL	9/8/20	
APPROVED			

TITLE SC TYPE ADAPTER, APC&PC, 1 PORTS, SHORT EARS, WITH SC CUCURBIT TYPE DUST CAP & SC TWO TYPE DUST CAP			
SIZE X	PART NO. OPSX1BNSC1NX		REV. -
REF: S00005C	SCALE: NTS	SHEET 1 OF 1	

6

5

4

3

2

1