






NUT



RECOMMEND PANEL CUT-OUT
MAX. PANEL THICKNESS: 0.200" [5.08]

NOTE:

MATERIAL

HOUSING:

PBT UL94V-0, BLACK

CONTACT:

BRASS

NUT:

BRASS

SHELL:

BRASS

O-RING:

NBR, BLACK

FINISH

CONTACT:

GOLD PLATED

OVER 50µ" NICKEL

NUT:

NICKEL PLATED

SHELL:

NICKEL PLATED

ELECTRICAL

RATED CURRENT:

1A

RATED VOLTAGE:

60V

INSULATION RESISTANCE:

100 MΩhms MIN.

CONTACT RESISTANCE:

10 mΩhms MAX.

WATER PROOF:

IP67



ENVIRONMENT

OPERATION TEMPERATURE:

-40°C TO +85°C

WIRE GAUGE:

28 AWG MAX RECOMMENDED



851-003-103R00Y

1 = GOLD FLASH
4 = 10µ" GOLD

RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-04-16

NorComp

SCALE:

NTS

SHEET

OF

1

1

REV

5

DWG NO.

851-003-103R00Y