

IE-PS-V14M-2SC-POF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

PushPull plug-in connector set according to IEC
61076-3-117 ver.14 (PROFINET), metal incl. SC insert

General ordering data

Version	FO connector, Version 14, SC-RJ POF, IP67
Order No.	1191550000
Type	IE-PS-V14M-2SC-POF
GTIN (EAN)	4032248974436
Qty.	10 pc(s).

IE-PS-V14M-2SC-POF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	79.9 mm	Depth (inches)	3.146 inch
Height	26.8 mm	Height (inches)	1.055 inch
Width	22.7 mm	Width (inches)	0.894 inch
Net weight	54.24 g		

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1	SCIP	e5bbf197-73b5-420b-90c0-0173b7b
------------	---	------	---------------------------------

General data

Colour	silver	Connection 1	SCRJ
Connection 2	Rapid connection system: crimping, cutting	Description of article	Version 14, SC-RJ POF
Fibre type	POF	Housing main material	Zinc diecast
Housing material, insert	PA, Zinc diecast	Insertion loss	≤ 1.0 dB
Plugging cycles	750	Protection degree	IP67
Sheath diameter, max.	10 mm	Sheath diameter, min.	5 mm

General standards

Certificate no. (cULus)	E316369	Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
-------------------------	---------	--------------------	---------------------------------------

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

IE-PS-V14M-2SC-POF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE
	MAN IE GUIDE EN
	Designation key / Type key
	Manual
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN
	PI PROFINET CABLING EN
	PI PROFINET CABLING EN

IE-PS-V14M-2SC-POF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

