




P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REV PER 063A-0485-01	21AUG01	JR	MS



26.92-26.67 [1.060-1.050]	33.66-33.40 [1.325-1.315]	53435-2
25.53-25.40 [1.005-1.000]	32.00-31.75 [1.260-1.250]	53435-1
'B'	'A'	AMP PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DK SCHRUM 17JUN96	AMP AMP Incorporated Harrisburg, PA 17105-3608				
DIMENSIONS: mm [INCHES]		CHK WJ VOCKROTH 25JUN96					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JL MECKLEY 25JUN96	NAME TERMINAL ASSEMBLY, QUICK-DISCONNECT, AMPOWER, WIRE SIZE: 500 MCM			
	0 PLC ±- 1 PLC ±- 2 PLC ±0.20 [0.008] 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC 108-13014	SIZE A2 CAGE CODE 00779 DRAWING NO C-53435			
			APPLICATION SPEC -				
	MATERIAL BODY & PINS BRASS PER QQ-B-626	FINISH SILVER PL 0.00127 [0.00050] MIN THK PER QQ-S-365	WEIGHT - lbs				
CUSTOMER DRAWING			SCALE 1:1 SHEET 1 OF 1 REV F				