

## RAFIX 16 - Selector switch, square collar, alignable without gaps, illuminated, momentary

**1.30.073.691/2000**

Only use contact blocks with momentary function.



### General information

|                   |                   |
|-------------------|-------------------|
| Actuator          | handle            |
| Marking of handle | translucent white |
| Form of collar    | square alignable  |

### Dimensions

|                   |                  |
|-------------------|------------------|
| Collar dimensions | 24.95 x 24.95 mm |
| Collar dimensions | 24.95 x 24.95 mm |
| Overall height    | 17.1 mm          |
| Mounting depth    | 44.7 mm          |
| Mounting hole     | 16.2 mm          |
| Key grid          | 25 x 25 mm       |

### Mechanical design

|                     |                            |
|---------------------|----------------------------|
| Mounting            | ring nut                   |
| Contact function    | momentary                  |
| Contact arrangement | according to contact block |
| Illumination        | yes                        |
| Rotating angle      | 2 x 40°                    |

### Mechanical characteristics

|             |        |
|-------------|--------|
| Torque max. | 1.3 Nm |
|-------------|--------|

### Other specifications

|                                                 |                                          |
|-------------------------------------------------|------------------------------------------|
| Operating life (operations)                     | 30,000 cycle                             |
| Degree of protection from front side            | IP65 (DIN EN 60529)                      |
| Operation temperature min.                      | -25 °C                                   |
| Ambient temp. operating max. without lamp / LED | +70 °C                                   |
| Ambient temp. operating max. with lamp /LED     | +55 °C                                   |
| Storage temperature min.                        | -40 °C                                   |
| Storage temperature max.                        | +85 °C                                   |
| Environmental resistance                        | acc. to IEC 60068-2-14, -30, -33 and -78 |
| ROHS compliant                                  | yes                                      |
| REACH compliant                                 | yes                                      |

## Panel cut-out

