



CUSTOMER PRINT


PART NUMBER: W6A8X-8PG-5XX_CD

NOTES:
1. ALL PARTS TO BE BULK PACKED.
2. SEE DRAWING HPMIMIX FOR HOLE PATTERN.
3. DIMENSIONS ARE FOR REFERENCE ONLY.

CONNECTOR P/N	POSITIONS		CONTACT STYLE	CABLE O.D. RANGE
	#16	#26		
W6A80-8PG-513	2	6	CRIMP	0.13-0.15" (3.3 -3.8 mm)
W6A80-8PG-516			CRIMP	0.16-0.18" (4.1 -4.6 mm)
W6A80-8PG-519			CRIMP	0.19-0.21" (4.8 -5.3 mm)
W6A80-8PG-522			CRIMP	0.22-0.25" (5.6 -6.3 mm)
W6A80-8PG-528			CRIMP	0.26-0.285" (6.6 -7.2 mm)
W6A82-8PG-513			SOLDER	0.13-0.15" (3.3 -3.8 mm)
W6A82-8PG-516			SOLDER	0.16-0.18" (4.1 -4.6 mm)
W6A82-8PG-519			SOLDER	0.19-0.21" (4.8 -5.3 mm)
W6A82-8PG-522			SOLDER	0.22-0.25" (5.6 -6.3 mm)
W6A82-8PG-528			SOLDER	0.26-0.285" (6.6 -7.2 mm)
NOTE: ADD SUFFIX "W" TO ANY CONNECTOR P/N ABOVE FOR WINGED COUPLING RING OPTION				



SHOWN ASSEMBLED
WITH STANDARD COUPLING RING



SHOWN ASSEMBLED
WITH WINGED COUPLING RING

RoHS COMPLIANT

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

PRELIMINARY

0A	PNK	01-16-16	PDR 14001 PRELIMINARY	
REV.	INIT.	DATE	DESCRIPTION	
			ORIG. DRAWN BY: PNK	DATE: 01-16-16
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			CHECKED BY:	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			APPROVED BY:	
CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			SCALE: NTS	SIZE: B
			SHEET: 1 OF 1	
			FILE: W6A8X-8PG-5XX_CD	DIRECTORY: SLW
			PART NUMBER: W6A8X-8PG-5XX_CD	REV: 0A
			TITLE: CABLE-END CONNECTOR 2-16 + 6-26 PIN CONTACTS MINI-CON-X POWER/SIGNAL	
			CUSTOMER: STANDARD PRODUCT	