

DESCRIPTION: M5 FEMALE - CABLE MOUNT - SOLDER CUP - 2 POSITION

NOTE:

MATERIAL

HOUSING: TPU, BLACK

CONTACT: BRASS

NUT: BRASS

O-RING: NBR, BLACK

FINISH

CONTACT: GOLD PLATED

OVER 50 μ NICKEL

NICKEL PLATED

NUT:

ELECTRICAL

RATED CURRENT: 1A

RATED VOLTAGE: 60V

INSULATION RESISTANCE: 100 M Ω hms MIN.


CONTACT RESISTANCE: 10 m Ω hms MAX.

WATER PROOF: IP67

ENVIRONMENT


OPERATION TEMPERATURE: -40°C TO +85°C

WIRE GAUGE: 28 AWG MAX RECOMMENDED





850-002-203RLUY

1 = GOLD FLASH
4 = 10 μ " GOLD



NUT



RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-03-16

NorComp

SCALE:
NTS

SHEET OF
1 1

REV
7

DWG NO.

850-002-203RLUY