

- 1
- CONNECTOR MAY BE FRONT OR REAR MOUNTED TO A MAXIMUM PANEL THICKNESS OF 3.2 mm.
2.
- PANEL NUT AND PANEL GASKET ARE PACKAGED UNASSEMBLED IN POLYBAG.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		A	REVISED PER ECO-09-009008	08APR2009	SS	MS

USB COUPLER
MATERIAL:
HOUSING-THERMOPLASTIC
CONTACTS-PHOSPHOR BRONZE
SHIELD-COPPER ALLOY
FINISH:
CONTACTS-GOLD OVER NICKEL
SHIELD-TIN OVER NICKEL

PANEL GASKET
MATERIAL: ELASTOMER
COLOR: BLACK

3.50
PANEL NUT
MATERIAL: BRASS
FINISH: NICKEL

RECEPTACLE HOUSING
MATERIAL: POLYESTER
COLOR: BLACK




SCALE 2:1

SCALE 2:1

SCALE 1:1

Ø 34.0
PANEL FLANGE

BAYONET LOCK



SUGGESTED
PANEL CUTOUT

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN RAGHU	03OCT06	 Tyco Electronics Harrisburg, PA 17105-3608			
				CHK J. LANDIS	03OCT06				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	-	NAME			
mm				PRODUCT SPEC		RECEPTACLE KIT, SERIES A TO SERIES A CIRCULAR SEALED USB CONNECTOR			
		0 PLC ±0.3 1 PLC ±0.2 2 PLC ±0.10 3 PLC ± 4 PLC ± ANGLES ±1°		108-2318					
				APPLICATION SPEC					
				114-13211		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL		FINISH		WEIGHT		A2	00779	C-1954643	-
						CUSTOMER DRAWING			
						SCALE		SHEET	OF
						5:2		1	1
								REV	A