


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION

F
E
D
C
B
A



Recommended Panel
Cut-Out










ABB-XXPMFS-SC7001
02:2Pin
:
03:3Pin



Pin Assignments Front View

- Note:
- * (QC) Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Gasket: Silicone, Gray
 - * Screw Nut: Nylon+GF, Black
 - * Use with waterproof cap or dust cap
Maximum Panel Thickness: 3.3mm
 - * Use without waterproof cap or dust cap
Maximum Panel Thickness: 4.5mm

UNIT:mm		TITLE STANDARD PANEL SCREW M CONN F PIN			
TOLERANCE		SCALE	SIZE	SHEET	OF
.X ±0.25		2:1	A4	1	1
.XX ±0.1		REV.	WC-REV.	QC: Inspection item	
.XXX ±0.05		A	A.1		
ANGLES ±1°					

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Jinhai	2015-07-06
ABB-XXPMFS-SC7001	CHECKED BY	DATE
CUSTOMER	Rensong	2015-07-06
ALTW	APPROVED BY	DATE
	Jerry	2015-07-06