

Han EMC 25 Base Panel



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 025 0301
Specification	Han EMC 25 Base Panel
HARTING eCatalogue	https://b2b.harting.com/09620250301

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] EMC
Type of hood/housing	Bulkhead mounted housing

Version

Size	16 A
Locking type	Single locking lever
Han-Easy Lock [®]	Yes
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94
(locking levers)

V-0

RoHS

compliant

ELV status

compliant

China RoHS

e

REACH Annex XVII substances

Not contained

REACH ANNEX XIV substances

Not contained

REACH SVHC substances

Yes

REACH SVHC substances

Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate

California Proposition 65 substances

Yes

California Proposition 65 substances

Nickel

Fire protection on railway vehicles

EN 45545-2 (2020-08)

Requirement set with Hazard Levels

R22 (HL 1-3)
R23 (HL 1-3)

Specifications and approvals

UL / CSA

UL 1977 ECBT2.E235076
CSA-C22.2 No. 182.3 ECBT8.E235076

Approvals

CE
DNV GL

Commercial data

Packaging size

1

Net weight

74.92 g

Country of origin

Germany

European customs tariff number

85389099

GTIN

5713140073432

ETIM

EC000437

eCl@ss

27440202 Shell for industrial connectors