

Han GND housing



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 0330
Specification	Han GND housing
HARTING eCatalogue	https://b2b.harting.com/09140010330

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® GND
Type of hood/housing	Bulkhead mounted housing

Version

Locking type	Snap-in latches
--------------	-----------------

Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Green
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

Commercial data

Packaging size	1
Net weight	13.42 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors