

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

D

REVISED & REDRAWN PER 0720-0856-96

21JUN96

DKS

WJV

STRAIGHT KNURL

5.61
[.221]
MAX DIA

21.46
[.845]
MAX

53853-2

AMP
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [INCHES]

MATERIAL

BRASS
PER QQ-B-626

TOLERANCES UNLESS
OTHERWISE SPECIFIED,

0 PLC ±-

1 PLC ±-

2 PLC ±0.20 [.008]

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH

SILVER PL
0.00508 [.000200] MIN
THK PER QQ-S-365

DWN
DK SCHRUM
21JUN96

CHK
WJ VOCKROTH
25JUN96

APVD
JL MECKLEY
25JUN96

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
— lbs

AMP Incorporated
Harrisburg, PA 17105-3608

PIN, QUICK-DISCONNECT,
AMPOWER™

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-53853

CUSTOMER DRAWING

SCALE
5:1

SHEET
1 OF 1

REV
D

AMP 1470-19 REV 09MAY94

21-JUN-96 13:56:35 amp26463 /files/dept1123/dwg1123/u.ampower/u.quick-disc