


MSOP-10 to DIP-14 SMT Adapter (0.5 mm pitch, 3.0 x 3.0 mm body)

REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		3.40				
B		1.00				
C		0.30				
B2		2.00				
C2		2.80				
D		0.20				
D2		0.70				
E		0.50				
F					0.600	
G					0.100	
H					0.025	



(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)