



BGA-4 to DIP-4 SMT Adapter (0.4 mm pitch, 0.88 x 0.88 mm body)




REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
C		0.22				
D		0.18				
E		0.40				
E2		0.40				
F					0.300	
G					0.100	
H					0.025	

Top View (SMT Footprint)




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)