

6

5

4

3





2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/9/20	

**SPECIFICATIONS:**

Material:

Housing: Alloy, rated UL 94V-0,

Sleeve: Zirconia ceramic

Electrical:

Repeatability: 1000 min times

Insertion loss: 0.3dB max

Interchangeability: 0.3dB max

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

MM	ANGLE
X. ± 0.35	X.° ± 2°
.X ± 0.30	.X° ± 1°
.XX ± 0.25	.XX° ± 0.5°
.XXX ± 0.15	.XXX° ± 0.5°

APPROVALS		DATE
DRAWN	LH	9/9/20
CHECKED	JL	9/9/20
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
OPTICAL SC/LC ADAPTERS, 1 PORTS , LONG-EARED
WITH CUCURBIT TYPE DUST CAP / LC DUST CAP

SIZE	PART NO.	REV.
X	OPSLN1ANNC1P2A	-
REF: S00005C	SCALE: NTS	SHEET 1 OF 1