






LOC		DIST		REVISIONS					
GP		00		REV	LYR	DESCRIPTION	DATE	DWN	APVD
				A		RELEASED PER ECO-10-025263	11FEB2011	CJV	JTL




- △ MATERIAL:
CAGE ASSEMBLY: NICKEL SILVER ALLOY, 0.25mm THK
GASKET RETENTION PLATE: STAINLESS STEEL
EMI GASKET: PLATED FILLED SILICONE.
- △ DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
3. MATES WITH SFP MSA COMPLIANT RECIEVERS.
- △ PADS AND VIAS CHASSIS GROUND.
5. INTERPRETATION OF DATUM REFERENCE FRAME IN ACCORDANCE WITH SECT 4.4.1.1 OR ASME Y14.5M-1994.
- △ MINIMUM PC BOARD THICKNESS:
SINGLE SIDED: 1.45mm
- △ HOLE PATTERN REPEATS FOR EACH PORT, SPACING BETWEEN PORTS IS 14.25mm.
- △ REFERENCE APPLICATION SPEC. 114-13120, HOLE A, FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- △ REFERENCE APPLICATION SPEC. 114-13120, HOLE B, FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.




RECOMMENDED BEZEL CUT-OUT
SCALE 4:1


0.23^{+0.10}_{-0.14}
TOP OF PCB
TO INSIDE OF
BEZEL CUTOUT



TYPICAL DIMENSIONS TO CHASSIS TO BE USED FOR THIS DRAWING. DIMENSIONS TO CHASSIS TO BE USED FOR THIS DRAWING. DIMENSIONS TO CHASSIS TO BE USED FOR THIS DRAWING. DIMENSIONS TO CHASSIS TO BE USED FOR THIS DRAWING.				DWN B. MCMASTER 02OCT08	Tyco Electronics Harrisburg, PA 17105-3608			
DIMENSIONS:				CHK M. SCHMITT 02OCT08	NAME SFP+ ENHANCED 1X2 CAGE ASSEMBLY, PRESS-FIT, EMI GASKET			
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD M. SCHMITT 02OCT08	SIZE A100779			
mm				PRODUCT SPEC	DRAWING NO			
0 PLC ±0.13				108-2364	C=2057555			
1 PLC ±0.1				APPLICATION SPEC	SCALE 6:1			
2 PLC ±0.08				114-13120	SHEET 1 OF 2			
3 PLC ±0.05				WEIGHT	REV A			
4 PLC ±0.05				CUSTOMER DRAWING				
ANGLES								
FINISH								



DETAIL G
SCALE 1/2" = 1'



-CROSS-HATCHED AREA DENOTES
COMPONENT AND TRACE KEEP-OUT
(EXCEPT CHASSIS GROUND)

THIS DRAWING IS A COMPUTER GENERATED DRAWING. NO REPRESENTATION OR WARRANTY IS MADE BY THE COMPANY FOR THE ACCURACY OF THE INFORMATION CONTAINED HEREIN. THE USER SHOULD BE CONTACTED FOR THE LATEST VERSION.		DWN MCMMASTER 020C108		 Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.13 1 PLC ± 0.1 2 PLC ± 0.08 3 PLC ± 0.05 4 PLC ± 0.5 ANGLES ± 1		NAME SFP+ ENHANCED I12 CAGE ASSEMBLY, PRESS-FIT, EMI GASKET	
		APPL M SCHMITT 020C108		SIZE CAGE CODE DRAWING NO A100779C-2057555	
MATERIAL -		FINISH -		RESTRICTED TO -	
		WEIGHT -		SCALE 6:1 SHEET 2 of 2 REV A	
CUSTOMER DRAWING					