






DESCRIPTION: RJ-45 TO 15-POSITION FEMALE D-SUB - PLASTIC & METALIZED PLASTIC

MATERIAL:

HOOD: ABS UL 94V-HB

RJADK15S70808Y1


SERIES _____
POSITIONS _____
15
GENDER _____
S = FEMALE
D-SUB TERMINALS _____
7 = CRIMP & POKE (CONTACTS PRE-CRIMPED)
MODULAR POSITIONS _____
08
MODULAR POSITIONS LOADED _____
08
COLOR _____
1 = BLACK
2 = METALIZED (SHIELD RATING: 60dB)
3 = GRAY
D-SUB CONTACT PLATING _____
1 = GOLD FLASH



RJ45

- 1. BLUE
- 2. ORANGE
- 3. BLACK
- 4. RED
- 5. GREEN
- 6. YELLOW
- 7. BROWN
- 8. WHITE

DB-15F



DO NOT SCALE FROM DRAWING

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 05-15-07	
		CHECKED:		DATE:	
NorComp		SCALE: N.T.S.	SHEET 1 OF 1		REV 1
		DWG NO. RJADK15S70808Y1			