



WQFN-14 (510BR) to DIP-18 SMT Adapter (0.5 mm pitch, 2.5 x 2.5 mm body)




REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		1.85				
A2		1.85				
B		0.58				
C		0.30				
B2		1.45				
C2		1.45				
D		0.20				
D2		0.20				
E		0.50				
F					0.600	
G					0.100	
H					0.025	

Top View (SMT Footprint)




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)