

har-port USB 3.0 A-A PFT white



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1919
Specification	har-port USB 3.0 A-A PFT white
HARTING eCatalogue	https://b2b.harting.com/09454521919

Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 3.0

Version

Connection type	Type A jack - type A jack
Fixing	Screwable in cover plates

Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	White
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	14 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140222939
ETIM	EC002599
eCl@ss	27060304 Appliance cord (data cable)