

## Han HighTemp 6B-asg1-LB-K-M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 806 2255
Specification	Han HighTemp 6B-asg1-LB-K-M20
HARTING eCatalogue	<a href="https://b2b.harting.com/19628062255">https://b2b.harting.com/19628062255</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® High Temp
Type of hood/housing	Surface mounted housing
Description of hood/housing	With metal cover
Type	Low construction

### Version

Size	6 B
Version	Side entry
Cable entry	1x M20
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +200 °C With Han® High Temp components
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	FPM
Colour (seal)	Red



**Pushing Performance**  
Since 1945

## Material properties

Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Commercial data

Packaging size	1
Net weight	239.56 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140132658
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors