







ADAPTER PLATE - HVP-HD1400 3POS HEADER INTERFACE




2399611-4	K/L/M	3POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING	M	PA66-GF	AQUA RED	(925)	1	12
			CODE HOUSING	L	PA66-GF	AQUA BROWN		1	11
			CODE HOUSING	K	PA66-GF	AQUA GREEN		1	10
			FOLLOW 2399611-1	-	-	-		-	1-9
2399611-3	G/H/J	3POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING	J	PA66-GF	ORANGE	(925)	1	12
			CODE HOUSING	H	PA66-GF	YELLOW		1	11
			CODE HOUSING	G	PA66-GF	RED		1	10
			FOLLOW 2399611-1	-	-	-		-	1-9
2399611-2	D/E/F	3POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING	F	PA66-GF	BROWN	(925)	1	12
			CODE HOUSING	E	PA66-GF	GREEN		1	11
			CODE HOUSING	D	PA66-GF	PURPLE		1	10
			FOLLOW 2399611-1	-	-	-		-	1-9
2399611-1	A/B/C	3POS,PIN DIA 14.0 HDR ASSY,90DEG	CODE HOUSING	C	PA66-GF	BLUE	(925)	1	12
			CODE HOUSING	B	PA66-GF	NATURE		1	11
			CODE HOUSING	A	PA66-GF	BLACK		1	10
			HEADER TPA	-	PA66-GF	RED		3	9
			FINGER PROTECTION CAP	-	PA66-GF	BLACK		3	8
			FACE SEAL	-	SILICONE	RED		1	7
			BUSBAR OVERMOLD,FRONT SIDE	-	-	-		3	6
			OUTER HOUSING	-	PA66-GF	BLACK		3	5
			INNER HOUSING	-	PA66-GF	BLACK		3	4
			HV INTERLOCK CABLE,BRIDGED	-	-	-		2	3
			HV INTERLOCK CABLE	-	-	-		2	2
			HEADER HOUSING 90DEG,3POS	-	AL-ALLOY	NICKEL PLATED		1	1
TE-ASSY-NO	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR	WEIGHT (g)	QTY	ITEM



1. MATING CONNECTOR REFER TO DRAWING 2400957
2. CODING VARIANT
3. FREE SPACE FOR HEADER
4. SEALING AREA AND BURR TOOL PARTING, SHRINKAGE, CAVITIES AND MARKS PERMITTED.
SURFACE ROUGHNESS Ra=1.6
5. DRAFT ANGLE UP TO 0.5° PERMITTED
6. MOUNTING SCREW M5
SCREW TYPE UP TO MANUFACTURER, DRILL HOLE DESIGN ACCORDING TO SCREW TYPE
7. MATERIAL: CORROSION RESISTANT, ELECTROCONDUCTIVE
8. SCREW M8 FOR BUSBAR CONNECTION
9. ALL THREAD HOLES ARE BLIND HOLES
10. INTERFACE PANEL CODE SEE SHEET 4

[illegible]

REVISONS				
P	LYN	DESCRIPTION	DATE	APPD
-		SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.				DESIGNED BY S. TAN	29DEC2021	TE Connectivity	
DIMENSIONS: (mm)				CHECKED BY J. L. L.	29DEC2021		
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APPROVED BY J. L. L.	29DEC2021		
				PRODUCT SPEC	1408-160407	NAME 3POS.PIN DIA 14.0.HDR ASSY.90DEG HVP-HD1400	
				APPLICATION SPEC	114-160222	SIZE CASE CODE DRAWING NO	
				WEIGHT	SEE TABLE	A 0 00779 C=2399611	
MATERIAL SEE TABLE				CUSTOMER DRAWING		RESTRICTED TO	
						SCALE 2:1	
						SHEET 6 OF 6	
						REV A.1	