




Pushing Performance  
Since 1945

# Circular Connector w. Harax M12 L3 M



Part number	21 03 241 1301
Specification	Circular Connector w. Harax M12 L3 M
HARTING eCatalogue	<a href="https://b2b.harting.com/21032411301">https://b2b.harting.com/21032411301</a>

## Identification

Category	Connectors
Series	Circular connectors M12
Identification	M12-L
Element	Cable connector
Specification	Straight

## Version

Termination method	HARAX® connection technology
Gender	Male
Shielding	Shielded
Number of contacts	2
Coding	B-coding
Locking type	Screw locking

## Technical characteristics

Conductor cross-section	0.25 ... 0.34 mm²
Conductor cross-section	AWG 24 ... AWG 22
Wire outer diameter	≤2.6 mm
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Overvoltage category	III
Insulation resistance	>10 <sup>8</sup> Ω



**Pushing Performance**  
Since 1945

## Technical characteristics

Contact resistance	≤10 mΩ
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	17
Limiting temperature	-40 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	4.5 ... 8.8 mm
Isolation group	I (600 ≤ CTI)

## Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Brass
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079



**Pushing Performance**  
Since 1945

## Commercial data

Packaging size	1
Net weight	55 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140137394
ETIM	EC002635
eCl@ss	27440116 Circular connector (for field assembly)