


| SIGN                                           | DATE     | DESCRIPTION                                               | APPROVER |
|------------------------------------------------|----------|-----------------------------------------------------------|----------|
| △                                              | 11/01'05 | Electrical standard changed.                              | Marvin   |
| △                                              | 04/20'06 | 2p to 6p with wedge is changed.                           | Marvin   |
| △                                              | 8/13'06  | Added VDE standard                                        | 梁仁松      |
| △                                              | 10/30'06 | Part No. is changed                                       | Marvin   |
| △                                              | 07/09`10 | The solid and Stranded wire are changed from16-26 to16-28 | Chen Bo  |
| △                                              | 07/09`10 | Rrmove the CSA mark                                       | Chen Bo  |
| △                                              | 08/12`13 | update the drawing                                        | Chen Bo  |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |          |                                                           |          |



TJ xx 11 x 3 xxxx G △



02 2 CONTACTS  
03 3 CONTACTS  
... ..  
24 24 CONTACTS

Color

0 Black (RAL9005)  
2 Red (RAL3001/D)  
3 Orange(RAL2011/P)  
4 Yellow(RAL1018/A)  
5 Green(RAL6018/T)  
6 Blue (RAL5015/A)  
8 Grey(RAL7035/D)  
9 White(RAL1102)  
△ C Green(RAL6018/U)

G RoHS compliant  
(lead<4%)  
In copper Alloy

0000 Standard @ Logo  
000A Standard ANY Logo  
0091 Standard ANY Logo  
Any special item by  
customer request,  
please contact sales  
department.



Material

- Item a Clamp: Brass(CuZn) Ni plated
- Item b Terminal screw: Steel Zinc plating “-” slot type
- Item c Female contact: PhBz ,Tin plated
- Item d Terminal (housing): PA66 (UL94V-0)
- Item e Terminal cover:PA66 (UL94V-0)

- △ △ △ Electrical cULus/VDE
- Voltage rating: 300VAC/300VAC
  - Current rating: 10A/10.5A
  - Wire range: 1.5mm<sup>2</sup>
  - Solid wire(AWG): 16-28
  - Stranded wire(AWG): 16-28
  - Torque: 3Lb-In/0.2Nm
  - Screw: M2
  - Wire strip length: 6-7mm
  - Withstanding Voltage: 1.6KV/2.5KV
  - Operating temperature: -40°C to +115°C
  - Safety Approval: cULus VDE
  - Critical dimension: △

N = Number of poles  
Dim A=Nx3.5  
Dim B=(N-1)x3.5

| Poles   | Dim A | Dim B |
|---------|-------|-------|
| 2p-6p   | ±0.15 | ±0.15 |
| 7p-12p  | ±0.20 | ±0.20 |
| 13p-18p | ±0.25 | ±0.25 |
| 19p-24p | ±0.30 | ±0.30 |

**ANYTEK**

CUSTOMER COPY  
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |         |                        |          |           |  |              |            |
|----------|---------|------------------------|----------|-----------|--|--------------|------------|
| TITLE    |         | TJ-3.5mm Series 2p-24p |          | DWG NO.   |  | 8TJ0501      |            |
| PART NO. |         | TJxx11x3xxxxG          |          | CUST NO.  |  |              |            |
| APPROVED | CHECKED | DESIGNED               | DRAWN    | Tolerance |  |              |            |
|          |         | Chen Bo                | Chen Bo  |           |  | UNIT: mm     | X. ±0.50   |
|          |         | 08/12`13               | 08/12`13 |           |  | SCALE: NONE  | X.X ±0.30  |
|          |         |                        |          |           |  | SHEET: 01/01 | X.XX ±0.10 |
|          |         |                        |          | REV.: H   |  | X° ±1°       |            |