




| 4      |          |     |               | 3                                              |
|--------|----------|-----|---------------|------------------------------------------------|
| ITEM # | PART #   | QTY | DESCRIPTION   | MATERIAL                                       |
| 1      | AP-176-1 | 1   | SHELL ASS'Y   | GLASS FILLED NYLON & 303 SS                    |
| 2      | AP-146-6 | 1   | INSERT ASS'Y  | DIALLYPHTHALATE, TYPE SDGF & GOLD PLATED BRASS |
| 3      | AP-105-5 | 1   | STRAIN RELIEF | NYLON                                          |
| 4      | AP-116-3 | 1   | WASHER        | RUBBER                                         |

NOTES:  
1) UNLESS OTHERWISE SPECIFIED, CONNECTOR MEETS ALL  
GENERAL REQUIREMENTS & SPECIFICATIONS OF MIL-C-55116



SECTION Z-Z

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

|      |             |      |              |      |                                                                                                                                                                                        |                 |                   |  |                 |  |                                              |  |
|------|-------------|------|--------------|------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-------------------|--|-----------------|--|----------------------------------------------|--|
|      |             |      |              |      | DWN.BY<br><b>SPL</b>                                                                                                                                                                   | DATE<br>8/20/18 | MATERIAL          |  |                 |  |                                              |  |
|      |             |      |              |      | CHECKED BY                                                                                                                                                                             | DATE            | FINISH            |  |                 |  |                                              |  |
|      |             |      |              |      | APPR.BY                                                                                                                                                                                | DATE            | WEIGHT —          |  | SCALE = 2.00 :1 |  | <b>NEXUS</b><br>STAMFORD,CONN                |  |
|      |             |      |              |      |                                                                                                                                                                                        |                 | TITLE             |  |                 |  |                                              |  |
|      |             |      |              |      | UNLESS OTHERWISE SPECIFIED:<br>DIMENSIONS ARE IN INCHES &/OR [mm]<br>TOLERANCES:<br>DECIMAL: .XX[X.X] .XXX[X.XX]<br>±.01[0.3] ±.005[0.13]<br><br>FRACTION: X/X ±1/64<br>ANGLES: .X ±.5 |                 | <b>AUDIO PLUG</b> |  |                 |  | SIZE<br><b>B</b><br>DWG. NO.<br>AP-176SPW-CP |  |
| A    | NEW RELEASE |      | 8/20<br>2018 | SPL  |                                                                                                                                                                                        |                 |                   |  |                 |  |                                              |  |
| LET. | REVISION    | CN # | DATE         | CHK. |                                                                                                                                                                                        |                 |                   |  |                 |  |                                              |  |