

D

D

C


C

B




B

A

A



MATING FACE



- 1

FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948. CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194, REAR GROMMET & INTERFACIAL SEAL: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.
- 2

PART TO MARKED WITH TE IDENTIFICATION, TE PART NO. AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.
- 3

THIS INSERT CONTAINS: 40 CAVITIES FOR SIZE 22 PIN CONTACTS
- 4

THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.

NON-ENV	GPRBN40PB	1738191-3
GROMMET ONLY	GPRBH40PB	1738191-2
ENVIRONMENTAL	GPRBE40PB	1738191-1
REMARKS	DESCRIPTIVE PART NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 10-4-10	TE Connectivity			
DIMENSIONS: mm		CHK K. HOGAN 10-4-10				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. HOGAN 10-4-10	NAME			
0 PLC ±-		PRODUCT SPEC	INSERT ASSEMBLY, PIN, ARRANGEMENT 40, KEY B, GPRB			
1 PLC ±0.1		APPLICATION SPEC				
2 PLC ±0.05			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC ±-			A2	00779	C-1738191	-
4 PLC ±-						
ANGLES ±1		WEIGHT				
FINISH		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV B	