

Adapter M12 RJ45 Cat 5a angled



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 381 4401
Specification	Adapter M12 RJ45 Cat 5a angled
HARTING eCatalogue	https://b2b.harting.com/21033814401

Identification

Category	Accessories			
Series	Circular connectors M12			
Type of accessory	M12 female-RJ45 panel feed through			
Description of the accessory	<table><tr><td>D-coding</td></tr><tr><td>4 poles</td></tr><tr><td>Angled</td></tr></table>	D-coding	4 poles	Angled
D-coding				
4 poles				
Angled				

Version

Gender	Female
--------	--------

Technical characteristics

Mating cycles	≥100
Thickness of the panel	2.1 ... 4.5 mm

Material properties

Surface (contacts)	Au over Ni Mating side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Material properties

ECHA SCIP number 0d7d3693-d625-47ab-934a-d241bf72c86e

California Proposition 65 substances Yes

California Proposition 65 substances Nickel
Lead

Specifications and approvals

UL / CSA UL 1977 ECBT2.E102079
CSA-C22.2 No. 182.3 ECBT8.E102079

PROFINET Yes

Commercial data

Packaging size 1

Net weight 47 g

Country of origin Romania

European customs tariff number 85389099

eCl@ss 27440292 Connector component (accessories)