

Han HP Base Panel



Image is for illustration purposes only. Please refer to product description.

Part number	09 39 024 0310
Specification	Han HP Base Panel
HARTING eCatalogue	https://b2b.harting.com/09390240310

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] HP
Type of hood/housing	Bulkhead mounted housing

Version

Size	24 B
Locking type	Screw locking
Field of application	Hoods/housings for rough environments

Technical characteristics

Tightening torque (screw locking)	3 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP66
	IP68
	IP69 / IPX9K acc. to ISO 20653

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE

Commercial data

Packaging size	1
Net weight	145.1 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140056725
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors