

IE-M12-PCBCE-PANEL-A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	PCB connection element M12, Solder connection, Cat.5 (ISO/IEC 11801), IP65 in acc. with DIN EN 60529
Order No.	1393470000
Type	IE-M12-PCBCE-PANEL-A
GTIN (EAN)	4050118194241
Qty.	10 pc(s).

IE-M12-PCBCE-PANEL-A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	12.2 g
------------	--------

Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	9229992a-00b9-4096-8962-200a7f3
------------	----------------	------	---------------------------------

Technical data of PCB plug-in connector

Coding	D	Number of poles	4
Protection degree	IP65 in acc. with DIN EN 60529	Housing main material	CuZn, Polyamide, nickel-plated
Connection thread	M12		

General Info

Connection 1	M12	Connection 2	Solder connection
Description of article	Connecting element, clip-on	Configuration	Reflow compatible
Housing main material	CuZn, Polyamide, nickel-plated	Category	Cat.5 (ISO/IEC 11801)
Connection thread	M12	Protection degree	IP65 in acc. with DIN EN 60529

Classifications

ETIM 6.0	EC002638	ETIM 7.0	EC003568
ETIM 8.0	EC003568	ECLASS 9.0	27-44-03-09
ECLASS 9.1	27-44-03-09	ECLASS 10.0	27-44-03-09
ECLASS 11.0	27-44-01-10	ECLASS 12.0	27-44-01-10

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN


IE-M12-PCBCE-PANEL-A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Dimensioned drawing



Dimensioned drawing



Drilling template

