

Han 3 EMC Hood Coupler 1 Lever PG 11



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 003 1750
Specification	Han 3 EMC Hood Coupler 1 Lever PG 11
HARTING eCatalogue	https://b2b.harting.com/09620031750

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] EMC
Type of hood/housing	Cable to cable housing

Version

Size	3 A
Version	Top entry
Cable entry	1x Pg 11
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44
	IP65 With seal screw
	IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted



Pushing Performance
Since 1945

Material properties

Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	CE
	DNV GL

Commercial data

Packaging size	10
Net weight	72.92 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140073135
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors