



Pushing Performance
Since 1945

Han 6EMC/B-HTE-M32 (HT)



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 806 0447
Specification	Han 6EMC/B-HTE-M32 (HT)
HARTING eCatalogue	https://b2b.harting.com/19628060447

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® EMC/B
	Han® High Temp
Type of hood/housing	Hood
Type	High construction

Version

Size	6 B
Version	Top entry
Cable entry	1x M32
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
	-40 ... +200 °C With Han® High Temp components
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
	IP66
Type rating acc. to UL 50 / UL 50E	4
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated



Pushing Performance
Since 1945

Material properties

Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

Commercial data

Packaging size	1
Net weight	110 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140132580
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors